



# E25: UC<sup>FIBRE</sup> Universal Central Tube B2ca Non-Metallic Gel-Filled Cable

**3000N, Ind/Out metal-free, Class B2<sub>ca</sub>-s1a-d1-a1, gel-filled, water-blocked central tube cable, up to 24 fibres, dielectric glass yarn armouring and FireRes<sup>®</sup> sheath.  
DIN/VDE: U-DQ(ZN)BH**



## Application and installation

This unitube cable can be used for LAN and WAN backbones, telecom access lines, fibre to business and fibre to the building drop connections; as well as fibre to the home drop and access connections.

Non-metallic unitube cable is with gel-filled tubes and water-blocked design. With its FireRes<sup>®</sup> sheathing this cable is ideal for indoor installations. It is CPR Class B2<sub>ca</sub> cable with very high flame retardant performance. It is glass yarn dielectric armoured for rodent resistance.

The cable is water-blocked and well suited for installation in ducts and on trays indoor and limited outdoor use in ducts.

## Standards

ISO 11801-1, EN 50173-1:2002, IEC 60794-1, EN50575

## Flame resistance

EN 50399: Class B2<sub>ca</sub> s1a-d1-a1, Class C<sub>ca</sub>, Class D<sub>ca</sub>, Class E<sub>ca</sub>  
LSHF-FR (FRNC): IEC 60332-1-2, IEC 60332-3-24, IEC 60754-2; IEC 61034

## Construction

Loose tube	Ø2.8 mm gel-filled loose tube for 2-24 Fibres			
Fibre colour code	1	Red	13	Red w/mark every 70mm
	2	Green	14	Green w/mark every 70mm
	3	Blue	15	Blue w/mark every 70mm
	4	Yellow	16	Yellow w/mark every 70mm
	5	White	17	White w/mark every 70mm
	6	Grey	18	Grey w/mark every 70mm
	7	Brown	19	Brown w/mark every 70mm
	8	Violet	20	Violet w/mark every 70mm
	9	Turquoise	21	Turquoise w/mark every 70mm
	10	Black	22	White w/mark every 35mm
	11	Orange	23	Orange w/mark every 70mm
	12	Pink	24	Pink w/mark every 70mm

## E25: UC<sup>FIBRE</sup> Universal Central Tube B2ca Non-Metallic Gel-Filled Cable

Strength member & Water-blocking	Water-blocking Glass yarns	
Cable Sheath colours	Cable with SM fibres: BendBright <sup>XS</sup> G.657.A2, BendBright G.657.A1	Yellow, RAL 1018
	Cable with OM1	Grey, RAL 7037
	Cable with MaxCap-BendBright-OM2	Orange, RAL 2009
	Cable with MaxCap-BendBright-OM3	Aqua, RAL 6027
	Cable with MaxCap-BendBright-OM4	Erika-Violet, RAL 4003
	Cable with BendBright WideCap-OM5	Lime-Green
Sheath	1.5 mm, FireRes <sup>®</sup> sheath, UV stabilised, EN 50290-2-27	
Sheath marking	Draka UC <sup>FIBRE</sup> I/O CT LSHF-FR B2ca-s1a-d1-a1 3.0 kN <Fibre count> <Fibre type> <Fibre brand> <Item No> <Factory Code> <Batch Number> <Meter mark> U-DQ(ZN)BH <Fibre count> <Fibre family> <Mode field diameter> /125 <Transmission Class>	

### Physical properties

IEC 60794-1-21/22

Nominal outer diameter	-	2 - 24 fibres: 7,5 mm
Nominal weight	-	2 - 24 fibres: 73 kg/km
Tensile strength (dynamic)	E1	3000 N (fibre strain ≤ 0,6%)
Tensile strength (permanent)	E1	1000 N (fibre strain ≤ 0,2%)
Compressive strength (crush)	E3	3000 N / 100 mm ( $\Delta\alpha$ reversible)
		1500 N / 100 mm (no attenuation change)
Torsion	E7	5 cycles ± 1 turn
Impact	E4	20 J (striking surface r=300 mm)
		5 J (striking surface r=12.5 mm)
Kink	E10	The cables do not form a kink when a loop is drawn together to a diameter of 100 mm
Min. permanent bending radius (unloaded)	E11	75 mm (> -20°C temperatures)
Min. installation bending radius (loaded)	-	150 mm
Temperature range	F1	Installation: -20°C to +60°C
		Storage: -40°C to +70°C Operation: -40°C to +70°C (in the case of ≤ -20°C temperature during operation, no sharp bends are allowed & bending radius > 150 mm for permanent)
Water penetration	F5B	No water on free end

# E25: UC<sup>FIBRE</sup> Universal Central Tube B2ca Non-Metallic Gel-Filled Cable

## Product codes – ordering information

Product Code	DoP Number*	Product Description	Fibre Count	Fibre Type	Fibre Data Sheet
60083160	1010613	UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 4 OM3B AQ	4	MaxCap-BB-OM3	C31
		UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 6 OM3B AQ	6	MaxCap-BB-OM3	C31
60090913	1011983	UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 8 OM3B AQ	8	MaxCap-BB-OM3	C31
60087031	1011299	UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 12 OM3B AQ	12	MaxCap-BB-OM3	C31
60083159	1010612	UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 24 OM3B AQ	24	MaxCap-BB-OM3	C31
		UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 4 OM4B 4003	4	MaxCap-BB-OM4	C32
60090914	1011984	UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 6 OM4B 4003	6	MaxCap-BB-OM4	C32
60083157	1010614	UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 8 OM4B 4003	8	MaxCap-BB-OM4	C32
60083157	1010614	UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 12 OM4B 4003	12	MaxCap-BB-OM4	C32
		UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 24 OM4B 4003	24	MaxCap-BB-OM4	C32
		UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 4 OM5B LG	4	WideCap-OM5	C39
		UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 6 OM5B LG	6	WideCap-OM5	C39
		UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 8 OM5B LG	8	WideCap-OM5	C39
		UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 12 OM5B LG	12	WideCap-OM5	C39
		UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 24 OM5B LG	24	WideCap-OM5	C39
60083197	1010670	UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 4 SM2D/A1 YL	4	OS2 BendBright G.657.A1	C17
		UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 6 SM2D/A1 YL	6	OS2 BendBright G.657.A1	C17
60090925	1011991	UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 8 SM2D/A1 YL	8	OS2 BendBright G.657.A1	C17
60083198	1010671	UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 12 SM2D/A1 YL	12	OS2 BendBright G.657.A1	C17
60083199	1010672	UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 24 SM2D/A1 YL	24	OS2 BendBright G.657.A1	C17
		UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 4 SM7A2 YL	4	OS2 BendBright <sup>XS</sup> G.657.A2	C24
		UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 6 SM7A2 YL	6	OS2 BendBright <sup>XS</sup> G.657.A2	C24
		UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 8 SM7A2 YL	8	OS2 BendBright <sup>XS</sup> G.657.A2	C24
		UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 12 SM7A2 YL	12	OS2 BendBright <sup>XS</sup> G.657.A2	C24
		UC <sup>FIBRE</sup> I/O CT LSHF-FR B2 3 kN 24 SM7A2 YL	24	OS2 BendBright <sup>XS</sup> G.657.A2	C24

\*DoP Numbers are per product code and any DoP number proves CPR approval for the cable. DoP files can be downloaded from the website: [www.prysmiangroup.com/cpr](http://www.prysmiangroup.com/cpr)

© PRYSMIAN GROUP 2018, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.